Document shredders DAHLE 514



- · High-volume department document shredder
- MHP® (Matrix High-Performance) cutting rollers: high-quality compound steel rollers for a guaranteed long service life
- Patented manufacturing process conserves resources by using significantly less raw material compared to production of traditional cutting rollers
- Higher performance thanks to MHP cutting rollers
- Separate CD feed opening and waste container for reliable, environmentally-friendly shredding
- Door open wide for easy emptying of waste container
- Intuitive, user-friendly illuminated control panel with audio signals
- Device shuts down automatically after 30 minutes without use
- Electronic start and stop function controlled by integrated light barrier

- Automatic paper reverse function clears excess paper
- Convenient feeding and reversing function for manual control
- Automatic safety shut-off when the waste container is full or the door is open
- · Optical waste level indicator
- · Pull-out waste container
- Powerful motor ensures high performance and longer run times
- · Extremely quiet operation
- Convenient swivel castors, two of which are lockable, with 5 cm ground clearance for greater mobility
- · Easy-to-reach main switch on rear of device
- Practical cold-device plug can be detached from document shredder

Article number	50522-13613
Entry width in mm	310
Sheet capacity (80g/sqm)*	17 - 19 sheets
Particle size (in mm)	2 x 15 mm
Security levels	P-5/F-2/O-4/T-5/E-4
Autom. oiler	-
Oil incl. in ml	50
running time	20min
CDs/DVDs	✓
Cards	✓
Paper clips	✓
Waste collection volume (in I)	140
Noise level when idle (db(A))	53
Power consumption (W)	900
Dimensions H x W x D (mm)	890 x 734 x 511
EAN	4009729062807



^{*} Maximum number of DIN A4 sheets that can be shredded in a single load under the following conditions: new cutting rollers (oiled if necessary), cold motor, power supply with rated voltage and rated frequency (230V/50Hz; 120V/60Hz). Sheet capacity may be lower and operating noise higher under different conditions. Sheet capacity may also vary due to sheet characteristics and paper feed.

